

For more information or support:

Philips Lighting B.V.
Zwaanhoefstraat 2
4702 LC Roosendaal
The Netherlands
Tel: +31 165 577906
Fax: +31 165 577907
Email: uvpurification@philips.com
www.philips.com/uvpurification

Advance Transformers Co.
Web: www.philips.com/uvpurification



The power to purify water and air with light

Philips lamp purification systems, protecting our world



©2006 Koninklijke Philips Electronics N.V.
All rights reserved.

Data subject to change
3222 635 61811
11/06

PHILIPS

Contents

- 3 Making the choice easy
- 4-7 Philips TUV low pressure mercury lamps
- 8-9 Philips medium pressure mercury lamps
- 10 Philips TUV eXtreme power technology amalgam lamps
- 11 Philips ozone generating lamps
- 12-14 Circuit information
- 15 Wiring diagrams
- 16 Philips TUV amalgam electronic drivers
- 17 Philips quartz sleeves

Making the choice easy

As the largest lamp manufacturer in the world, we bring you the very best in product innovation, reliability and quality. Using the knowledge of lighting technology that we have built up for more than 100 years, we offer a comprehensive portfolio of ultraviolet (UV) lamps and ballast systems for a wide range of applications. From water and air purification to insect traps, colored lamps, aquariums, UV curing, blacklight blue and reprography.

We offer you a comprehensive choice from low pressure mercury lamps, quartz medium pressure lamps to high output amalgam lamps, ideal for use across a range of applications where purification is required. Complimentary to this lamp range, Philips offers a wide variety of ballasts and sleeves.

We invented and pioneered the use of technology to reduce the mercury level of our lamps. As a result, we are very proud to have by far the lowest mercury level in ultraviolet (UV) lamps in the industry.



Philips TUV low pressure mercury lamps

Philips tubular ultraviolet (TUV) purification lamps help protect our world by de-activating bacteria, viruses and other primitive organisms safely and economically. Also effective when organisms have become immune to other purifying methods, Philips TUV lamps are ideal for use across a range of applications with the ability to purify air, water and surfaces.

From hospitals to laboratories. From food processing industries such as dairies, breweries and bakeries to cold storage rooms and air conditioning systems, Philips TUV lamps are the safe solution, making our surroundings cleaner, safer and more hygienic.



The technology behind Philips TUV lamps provides purification without the addition of chemicals. That makes it an ideal solution for residential and industrial water purification. You will also find that our lamps are used to make our swimming pools, ponds and aquariums cleaner.

Please contact us for tailor made solutions. Lamp life in hours and UVC output in Watts were measured with lamps operated under laboratory conditions. For reference purposes only. Actual life and output depends on operating conditions.

Bf-Bf = Base face - Base face
Bf-Te = Base face - Tube end



Note: Radiation from UVC lamps is harmful to eyes and skin.
Equipment using these lamps must screen completely from direct view.




Philips TUV low pressure straight tube lamps

Philips is the largest manufacturer of standard low pressure mercury lamps. These Philips TUV lamps consist of a tubular glass envelope emitting short-wave ultraviolet (UV) radiation with a peak at 254 nm (UVC) for germicidal action. The Philips in-house made glass filters out the 185 nm ozone forming line thus preventing the creation of ozone. High Output (HO) versions are available limiting required space and the footprint of your systems. Low pressure mercury lamps are very efficient, up to 40%. A protective coating on the inside limits the depreciation of the useful UVC output. This allows application manufacturers to design their systems to the highest efficiency. Philips invented and pioneered the use of technology to reduce the mercury level of the lamps. As a result this has been brought down to by far the lowest mercury level in UV lamps in the industry.

- Main applications:
- Residential drinking water units
 - Stand alone air purifiers
 - Wall-mounted air purification units

Features	Benefits
Coating on the inside	The UVC output over lifetime remains constant, allowing optimal design of the water/air treatment unit.
Lowest mercury level	More environmentally friendly



Philips TUV lamps											
Type	Cap/ base	Tube diameter max.	Arc length mm (X)	Bf - Bf mm (A)	Lamp Wattage (W)	Lamp voltage (V)	Lamp current (A)	UVC 100h (W)	µW/cm² at 1 meter	Depreciation 9000 h %	Useful lifetime h
Philips TUV 4W	G5	16.0	85	135.9	4	29	0.17	0.9	9	40	6000
Philips TUV 6W	G5	16.0	161	212.1	6	42	0.16	1.5	15	25	9000
Philips TUV 8W	G5	16.0	237	288.3	7	56	0.15	2.1	21	20	9000
Philips TUV 10W	G13	28.0	262	331.5	9	45	0.23	2.2	23	15	9000
Philips TUV 11W	G5	16.0	161	212.1	11	33	0.41	2.6	26	30	9000
Philips TUV 15W	G13	28.0	373	437.4	15	51	0.34	4.7	48	10	9000
Philips TUV 16W	G5	16.0	237	288.3	16	49	0.39	3.9	39	20	9000
Philips TUV F17T8	G13	28.0	526	589.8	17	72	0.27	4.5	45	20	9000
Philips TUV 25W	G5	16.0	466	516.9	28	68	0.49	8.8	88	20	9000
Philips TUV 25W	G13	28.0	373	437.4	24	46	0.61	7.0	69	15	9000
Philips TUV 30W	G13	28.0	831	894.6	30	100	0.37	11.2	100	10	9000
Philips TUV 36W	G13	28.0	1135	1199.4	36	103	0.44	15.3	145	10	9000
Philips TUV 55W HO	G13	28.0	831	894.6	54	86	0.77	18.0	150	10	9000
Philips TUV 75W HO	G13	28.0	1135	1199.4	75	110	0.84	26.0	220	10	9000
Philips TUV 115W RVHO	G13	40.5	1037	1199.4	115	92	1.50	33.5	610	20*	5000
Philips TUV 115WVHO	G13	40.5	1037	1199.4	115	92	1.50	38.8	360	15*	5000



*at 5000 hours

Philips TUV low pressure PL-S and PL-L lamps

These lamps combine all the benefits listed in the previous part and have on top of that, a very compact design. This allows the possibility of a compact unit design. Another advantage is that the lamps are single ended and can be easily replaced. The HO versions are very efficient in air purification applications as they are windchill corrected. This means that in the cooling air flow the lamp will be operating at their optimal temperature range thus giving the highest efficiency. The Philips TUV PL-S lamps have specially adapted starters providing almost instant starting characteristics already built into the lamp base.

- Main applications:
- Residential drinking water
 - Pond water
 - In-duct air treatment units
 - Stand alone air purifiers

Features	Benefits
Compact design	Small footprint for system, design flexibility
Single-ended	Easy lamp replacement
Wind-chill corrected versions	Optimal application performance, better use of lamps, fewer lamps needed



Philips TUV PL-S lamps												
Type	Cap/ base	Tube diameter max. mm (D)	Tube diameter I max. mm (DI)	Arc length mm	Bf -Te mm	Lamp Wattage (W)	Lamp voltage (V)	Lamp current (A)	UV-C I00h (W)	µW/cm² at I meter	Depreciation 9000 h %	Useful lifetime h
Philips TUV PL-S 5W 2 pin	G23	28.0	13.0 fig.1	85	82.5	5	35	0.18	1.0	9	20	9000
Philips TUV PL-S 7W 2 pin	G23	28.0	13.0 fig.1	145	112.5	7	46	0.18	1.6	15	20	9000
Philips TUV PL-S 9W 2 pin	G23	28.0	13.0 fig.1	210	144.5	9	60	0.17	2.4	22	20	9000
Philips TUV PL-S 9W 4 pin	2G7	28.0	13.0 fig.2	210	144.5	9	60	0.17	2.4	22	20	9000
Philips TUV PL-S 11W 2 pin	G23	28.0	13.0 fig.1	350	213.3	11	89	0.16	3.6	33	20	9000
Philips TUV PL-S 13W 2 pin	GX23	28.0	13.0 fig.3	230	155.2	13	56	0.29	3.4	31	20	9000
Philips TUV PL-L lamps												
Philips TUV PL-L 18W 4 pin	2G11	39.0	18.0 fig.4	325	220.0	18	58	0.37	5.5	51	15	9000
Philips TUV PL-L 24W 4 pin	2G11	39.0	18.0 fig.4	515	315.0	24	87	0.35	7.0	65	15	9000
Philips TUV PL-L 35W HO 4 pin ⁽¹⁾	2G11	39.0	18.0 fig.4	325	220.0	38	55	0.85	11.0	105	15	9000
Philips TUV PL-L 36W 4 pin ⁽²⁾	2G11	39.0	18.0 fig.4	705	410.0	36	106	0.44	12.0	110	15	9000
Philips TUV PL-L 55W HF 4 pin ⁽¹⁾	2G11	39.0	18.0 fig.4	955	535.0	55	105	0.53	17.0	156	15	9000
Philips TUV PL-L 60W HO 4 pin ^{(1) (2)}	2G11	39.0	18.0 fig.4	705	410.0	60	118	0.68	18.0	166	15	9000
Philips TUV PL-L 95W HO 4 pin ⁽¹⁾	2G11	39.0	18.0 fig.4	955	535.0	90	115	0.80	27.0	250	15	9000



1) When used with electronic ballast 25 KHz HF
2) Lamp is also available with shatterproof SECURA sleeve

Philips TUV low pressure lamps - T5 range

The Philips TUV T5 range uses a smaller diameter glass tube than the conventional straight tube lamps. They come in a variety of sizes, end caps and output versions. From single pin to single ended and from normal output to HO, guaranteeing that there is a suitable lamp for every application. The extreme low mercury in the lamps has allowed us to bring the first lamps on the market that are compliant to the strict TCLP regulations, and are considered as non hazardous waste.

- Main applications:
- Municipal water treatment systems
 - Swimming pool applications
 - Residential drinking water systems
 - Air treatment units

Features	Benefits
Small diameter	Small footprint for system, design flexibility
Some TCLP compliant lamps	Can be disposed as non toxic waste



Philips TUV T5 lamps										
Type	Cap/ base	Arc length mm (X)	Bf - Bf mm (Y)	Lamp Wattage (W)	Lamp voltage (V)	Lamp current (A)	UV-C I00h (W)	µW/cm² at I m	Depreciation 9000 hr %	Useful lifetime h
Philips TUV 36 T5 SP*	single pin	762	842.4	40	94	0.43	15.0	144	15	9000
Philips TUV 64 T5 SP*	single pin	1473	1553.6	75	176	0.43	31.0	280	15	9000
Philips TUV 64 T5 HO SP*	single pin	1459	1553.6	145	175	0.80	48.0	442	20	9000
Philips TUV 11W 4P-SE**	4 pin single ended	161	241.1	11	33	0.41	2.6	26	30	9000
Philips TUV 16W 4P-SE**	4 pin single ended	237	317.3	16	49	0.39	3.9	39	20	9000
Philips TUV 25W 4P-SE**	4 pin single ended	466	545.9	28	68	0.49	8.8	88	20	9000
Philips TUV 36 T5 4P-SE*	4 pin single ended	762	842.4	40	94	0.43	15.0	144	15	9000
Philips TUV 36 T5 HO 4P-SE*	4 pin single ended	748	842.4	75	97	0.80	25.0	230	20	9000
Philips TUV 64 T5 4P-SE*	4 pin single ended	1473	1553.6	75	176	0.43	31.0	280	15	9000
Philips TUV 64 T5 4P-SE CS*	4 pin single ended	1473	1553.6	75	176	0.43	31.0	280	15	9000
Philips TUV 64 T5 HO 4P-SE*	4 pin single ended	1459	1553.6	145	175	0.80	48.0	442	20	9000

* When used with electronic ballast 25 KHz HF
** When used with conventional magnetic ballast 50 Hz

Philips medium pressure mercury lamps


We manufacture and internationally distribute a wide range of high quality medium pressure mercury UV lamps. These quartz lamps are available up to 120 Watts per cm, with an arc length of 4 to 140 cm, in a variety of end fittings. The lamps are made from selected types of quartz glass, manufactured at our own factories.

Medium pressure mercury UV lamps

Our medium pressure lamps contain sophisticated quantities of mercury bromides, providing a self-cleaning halogen cycle, to control the decline of UV radiation over lamp life.

Main applications:


- Municipal waste water treatment systems
- Municipal drinking water treatment systems
- Process water treatment systems
- Swimming pool treatment systems



Spectral output


The lamps emit the characteristic spectrum of mercury discharge lamps. The HOK and HTK types also radiate wavelengths below 240 nm, whereby ozone is formed. The special quartz of the HTQ lamps absorbs radiation below 240 nm.

Features	Benefits
Self cleaning halogen cycle	Better maintenance of lamps, no over-designing necessary, cost saving




Philips HOK lamps										
Type	Tube diameter mm	Arc length mm (X)	Lamp wattage (W)	Lamp voltage (V)	Overall lamp length (Y)	Lamp current (A)	UVC >210 nm (W)	UVB (W)	UVA (W)	µW/cm² at 1 meter
Philips HOK 4/120	14	29	400	125	104.0	3.5	53	32	31	488
Philips HOK 4/120 SE*	14	29	400	125	110.0	3.5	53	32	31	488
Philips HOK 20/100	22	195	2000	245	262.0	9.6	325	198	175	2990
Philips HOK 35/120	22	348	4300	510	428.0	10.3	759	403	351	6983
Philips HOK 50/120	22	500	6000	1050	580.0	10.0	1060	546	462	9752
Philips HOK 65/120	22	637	7800	910	717.0	10.3	1278	741	722	11758
Philips HOK 80/120	22	800	9600	1080	880.0	10.5	1568	926	829	14426
Philips HOK 105/120	22	1057	12400	1430	1137.0	10	2021	1244	1042	18593
Philips HOK 140/120	22	1407	17000	1920	1487.0	10.0	2860	1646	1380	26312
Philips HTK 7/60	14	700	4000	1400	770.0	3.1	593	380	321	5456
Philips HTQ 7	14	700	2000	1400	762.5	1.7	130	165	142	1196
Philips HTQ 14	22	1400	4000	1400	1485.0	3.1	280	350	300	2576
Philips HOK 10/120L	22	106	1000	145	232.0	7.5	135	80	80	1250
Philips HOK 15/120L	22	151	1450	150	277.0	10.0	185	135	128	1720
Philips HOK 20/120L	22	204	2000	240	332.0	9.7	280	180	175	2570
Philips HOK 25/120L	22	254	2800	275	382.0	10.0	466	280	255	4290


* SE = single ended **Note:** Permissible bulb temperatures: HOK: 600 - 900°C HTK, HTQ: 500 - 700°C
Permissible pinch temperatures: 300°C
Please contact us for details on dimensions and tolerances




Philips HOK 4/120




Philips HOK 4/120 SE




Philips HOK 20/100




Philips HOK 35/120, HOK 50/120, HOK 65/120, HOK 80/120, Philips HOK 105/120, HOK 140/120



Philips HTK 7/60



Philips HTQ 7, HTQ 14



Philips HOK 10/120L, HOK 15/120L, HOK 20/120L, HOK 25/120L

Note: please contact us for details on dimensions and tolerances.

Philips TUV extreme power technology amalgam lamps

Philips amalgam lamps combine the advantages of the low pressure and the medium pressure lamp. This fills the gap between the low pressure and medium pressure applications. The amalgam lamp combines high efficiencies with relative high power densities operating in a broad temperature range.





By using our long history of lamp development we offer a lamp with a very high UVC efficiency. By applying our patented coating technology we are able to guarantee a maintenance of 85% after 12000 hours operating in a broad temperature range.

Our special amalgam gives a broader temperature range in which lamps operate most efficiently.

- Main applications:
- Municipal drinking water treatment systems
 - Municipal waste water treatment systems
 - Process water treatment units
 - Swimming pool treatment systems

eXtreme Power Technology (XPT) amalgam lamps
This cutting edge technology allows high wattage in all low pressure lamps, resulting in amazing power.

Features	Benefits
Special amalgam used	Highest efficiency in broader temperature range, allowing greater flexibility in system design and application
Coating on inside	Low UVC depreciation so over-designing the system can be limited to the bare minimum



Philips amalgam lamps										
Type T10	Cap/ base	Tube diameter (A)	Arc length mm (B)	Basephase max mm (C)	Lamp Wattage (W)	Lamp voltage (V)	Lamp current (A)	UVC 100h (W)	Maintenance 12000 h %	Useful lifetime h
Philips TUV 330W XPT		32.0	1440	1560	325	72	4.6	107	85	12.000
Philips TUV 270W XPT		32.0	1440	1560	268	78	3.5	100	85	12.000
Type T8										
Philips TUV 235W XPT		25.5	1410	1510	255	83	3.1	90	85	12.000
Type T6										
Philips TUV 325W XPT	G10.2q	19.0	1480	1580	280	141	2.0	100	85	12.000
Philips TUV 240W XPT	G10.2q	19.0	1480	1600	243	134	1.8	86	85	12.000
Philips TUV 130W XPT	G10.2q	19.0	740	840	146	71	2.1	50	85	12.000

Electrical values depend on power supply. **Note:** please contact us for tailor made solutions.




Philips ozone generating lamps

Ozone is one of the most powerful oxidants known and the naturally occurring level not only protects all life from the harmful effects of solar ultraviolet radiation but also is very effective at destroying bacteria and viruses.

Philips ozone generating lamps are effective in producing the very precise wavelength of electromagnetic radiation required in this process, eliminating harmful substances and pollutants. That is why Philip's ozone lamps are ideal across a range of applications, from swimming pools to water treatments.

- Main applications:
- Ultra Pure process water treatment systems
 - Swimming pool and spa water treatment units
 - Total Organic Compound (TOC) reducing applications
 - In duct air treatment units

Features	Benefits
Ability to measure 185nm	Ability to select most optimal lamp per application



Philips TUV ozone lamps										
Type T10	Cap/ base	Tube diameter (A)	Arc length mm (B)	Basephase max mm (C)	Lamp Wattage (W)	Lamp voltage (V)	Lamp current (A)	185 nm UVC 100h (W)	Maintenance 12000 h %	Useful lifetime h
Philips TUV 330W ozone		32.0	1440	1560	325	72	4.6	13.3	80	12.000
Philips TUV 270W ozone		32.0	1440	1560	268	78	3.5	12.4	80	12.000
Type T8										
Philips TUV 235W ozone		25.5	1410	1510	255	83	3.1	11.2	80	12.000
Type T6										
Philips TUV 325W ozone	G10.2q	19.0	1480	1580	280	141	2.0	12.4	80	12.000
Philips TUV 240W ozone	G10.2q	19.0	1480	1600	243	134	1.8	10.7	80	12.000
Philips TUV 130W ozone	G10.2q	19.0	740	840	146	71	2.1	6.3	80	12.000

Electrical values depend on power supply. **Note:** please contact us for tailor made solutions.

Circuit information

Supply Voltage 230V (50Hz)

Type		# Lamps	Starter	*Capacitor (uF)	Electromagnetic ballast ^{1) 2)}	EOC	Circuit Number (Page 15)
Philips TUV 4W	T5	1	S2	2.0 paral.	BTL 8W 230V B2	928122 30	1
		2	2*S2	2.0 paral.	BTL 8W 230V B2	928122 30	2
Philips TUV 6W	T5	1	S2	2.0 paral.	BTL 8W 230V B2	928122 30	1
		2	2*S2	2.0 paral.	BTL 13W 230V B2	928245 30	2
Philips TUV 8W	T5	1ft	1	S2	2.0 paral.	BTL 8W 230V B2	928122 30
			1	S2	2.0 paral.	BTL 13W 230V B2	928245 30
			2	2*S2	1.6 paral.	BTL 13W 230V B2	928245 30
Philips TUV 11W	T5		1	S10	4.5 paral.	BTL 8W 230V B2 (2*/I)	928122 30
			1	S10	4.5 paral.	BTA 18W 230V C	919120 30
Philips TUV 16W	T5	1ft	1	S10	4.5 paral.	BTA 18W 230V C	919120 30
			2	2*S2	4.5 paral.	BTA 30W 230V C	919151 30
Philips TUV 25W	T5		1	S10	4.5 paral.	BTA 18W 230V C	919120 30
Philips TUV 10W	T8		1	S10	2.0 paral.	BPL 18W 230V B2	928306 30
Philips TUV 15W	T8		1	S10	4.5 paral.	BTA 15W 230V B2	919106 30
Philips TUV 25W	T8		1	S10	4.5 paral.	BTA 36W 230V C	919175 30
Philips TUV 30W	T8	3ft	1	S10	4.5 paral.	BTA 30W 230V C	919151 30
Philips TUV 36W	T8	4ft	1	S10	4.5 paral.	BTA 36W 230V C	919175 30
Philips TUV 55W HO	T8	3ft	1	S10	6.5 paral.	BTA 58W 230V B2	919229 30
Philips TUV 75W HO	T8	4ft	1	S12	2 x 4.5 paral.	BTA 36W 230V C (2*/I)	919175 30
			1	S12		VS L80.397	Vossloh-Schwabe
Philips TUV 115W VHO	T12	4ft	1	CP	2 x 9 paral.	VS L140 UV 799	Vossloh-Schwabe
			1	S12	2 x 4.5 paral.	BTA 58W 320V B2 (2*/I)	919229 30
Philips TUV 11W 4P-SE	T5		1	S10	4.5 paral.	BTL 8W 230V B2 (2*/I)	919122 30
			1	S10	4.5 paral.	BTA 18W 230V C	919120 30
Philips TUV 16W 4P-SE	T5		1	S10	4.5 paral.	BTA 18W 230V C	919120 30
			2	2*S2	4.5 paral.	BTA 30W 230V C	919151 30
Philips TUV 25W 4P-SE	T5	2ft	1	S10	4.5 paral.	BTA 36W 230V C	919175 30
Philips TUV 36T5 4P-SE	T5	3ft	1	S10	4.5 paral.	BTA 36W 230V C	919175 30
Philips TUV 36T5 HO 4P-SE	T5	3ft	1	S10	9 paral.	VS L80.397	Vossloh-Schwabe
Philips TUV PL-S 5W 2P			1	N.A.		BPL 11W 230V B1	928184 30
			2	N.A.		BPL 11W 230V B1	928184 30
Philips TUV PL-S 7W 2P			1	N.A.		BPL 11W 230V B1	928184 30
			2	N.A.		BTL 13W 230V B2	928245 30
Philips TUV PL-S 9W 2P			1	N.A.		BPL 11W 230V B1	928184 30
			2	N.A.		BTL 13W 230V B2	928245 30
Philips TUV PL-S 11W 2P			1	N.A.		BPL 11W 230V B1	928184 30
Philips TUV PL-L 18W 4P			1	S10	4.5 paral.	BTA 18W 230V C	919120 30
			2	2*S2	4.5 paral.	BTA 36W 230V C	919175 30
Philips TUV PL-L 24W 4P			1	S10	4.5 paral.	BTA 30W 230V C	919151 30
Philips TUV PL-L 36W 4P			1	S10	4.5 paral.	BTA 36W 230V C	919175 30
Philips TUV PL-L 60W HO 4P			1	S10	6.5 paral.	BTA 58W 230V B2	919229 30

N.A. Starter is implemented

CP 100-180W Philips Cleo Power bimetal starter

*Voltage values for Capacitors: Parallel: 250Vrms, series: 450Vrms

1) To support the existing lamp types as listed for special lighting applications, the specified ballast types are approved for use in special lamp-ballast combinations. Because these ballasts are not specially designed for operating the listed lamp types, the applicability of these solutions is not guaranteed for the future. Despite our efforts to ensure backwards-compatibility, the specifications of the future ballast types may change so that these no longer support the special lamp as listed.

2) We will publish written notifications when such changes occur, resulting in the inability to support specific lamp-ballast combinations.

Supply Voltage 230V (50Hz)

Type		# Lamps	Electronic ballast	EOC	Circuit Number (Page 15)
Philips TUV 4W	T5	1	HF-MboxBLUE 105 TL/PL-S (square / linear)	53672330 / 53678530	6
Philips TUV 6W	T5	1	HF-MboxBLUE 109 TL/PL-S (square / linear)	53674730 / 53680830	6
Philips TUV 8W	T5	1ft	HF-MboxRED 109 TL/PL-S (square)	93142930	6
Philips TUV 11W	T5		HFP 1 24-39 TL5 HO	928573	6
			HFP 2 24-39 TL5 HO	928658	7
Philips TUV 16W	T5	1ft	HFP 1 24-39 TL5 HO	928573	6
			HFP 2 24-39 TL5 HO	928658	7
Philips TUV 25W	T5		HFP 1 24-39 TL5 HO	928573	6
			HFP 2 24-39 TL5 HO	928658	7
Philips TUV 10W	T8		HF-P 118 PL-T/C	74939030	6
Philips TUV 15W	T8		HF-P 118 TLD E11	93408630	6
			HF-P 218 TLD E11	93413030	7
Philips TUV 25W	T8		HFP 1 60-120 PL-H	92875731	6
Philips TUV 30W	T8	3ft	HF-P 136 TLD E11	93146730	6
Philips TLD 36W	T8	4ft	HF-P 136 TLD E11	93146730	6
			HF-P 236 TLD E11	93150430	7
Philips TUV 55W HO	T8	3ft	HFP 1 60-120 PL-H	92875731	6
			IUV-2S60-M4LD (120-277V main)	ADVANCE	6
Philips TUV 75W HO	T8	4ft	HFP 1 60-120 PL-H	92875731	6
			IUV-2S60-M4LD (120-277V main)	ADVANCE	6
Philips TUV 115WVHO	T12	4ft	EVG 1.4-1.5A (Instant Start four wires)	ZED Germany	6
Philips TUV 11W 4P-SE	T5		HFP 1 24-39 TL5 HO	928573	6
			HFP 2 24-39 TL5 HO	928658	7
Philips TUV 16W 4P-SE	T5		HFP 1 24-39 TL5 HO	928573	6
			HFP 2 24-39 TL5 HO	928658	7
Philips TUV 25W 4P-SE	T5	2ft	HFP 1 24-39 TL5 HO	928573	6
			HFP 2 24-39 TL5 HO	928658	7
Philips TUV 36T5 4P-SE	T5	3ft	HF-B 158 TLD E11	93156630	6
			HFPI 54 TL5 HO	928610	6
			HF-P 136 TLD E11	93146730	6
Philips TUV 36T5 HO 4P-SE	T5	3ft	HFP 1 60-120 P-LH	92875731	6
			IUV-2S60-M4LD (120-277V main)	ADVANCE	6
Philips TUV 64T5 4P-SE	T5	5ft	HFPI 54TL5 HO	928610	6
Philips TUV 64T5 HO 4P-SE			IUV-2S60-M4LD (120-277V main)	ADVANCE	6
Philips TUV PL-S 9W 4P			HF-MboxBLUE 109 TL/PL-S (square / linear)	53674730 / 53680830	8
Philips TUV PL-L 18W 4P			HF-MboxRED 109 TL/PL-S (square)	93142930	8
			HF-P 1 18-24 PL-L	749376	8
Philips TUV PL-L 18W 4P			HF-P 2 18-24 PL-L	749703	9
Philips TUV PL-L 24W 4P			HF-P 1 18-24 PL-L	749376	8
			HF-P 2 18-24 PL-L	749703	9
Philips TUV PL-L 35W HO 4P			HF-P 1 60-120 PL-H	92875731	8
			IUV-2S60-M4LD (120-227V main)	ADVANCE	8
			IUV-2S60-M4LD (120-277V main)	ADVANCE	9
Philips TUV PL-L 36W 4P			HF-P 136 PL-L E11	934178 30	8
			HF-P 236 PL-L E11	934253 30	9
Philips TUV PL-L 55W HF 4P			HF-P 155 PL-L E11	934239 30	8
			HF-P 255 PL-L E11	934291 30	9
Philips TUV PL-L 60W HO			HF-P 1 60-120 PL-H	92875731	8
			IUV-2S60-M4LD (120-277V main)	ADVANCE	8
			IUV-2S60-M4LD (120-277V main)	ADVANCE	9
Philips TUV PL-L 95W HO			HF-P 1 60-120 PL-H	92875731	8
			IUV-2S60-M4LD (120-277 main)	ADVANCE	8

Supply Voltage 120V (60Hz)



Type			Base-face length (mm)	# Lamps	Electromagnetic ballast ^{1) 2)} Advance Transformers Co.	Electronic ballast ^{1) 2)} Advance Transformers Co.	Electronic ballast ^{1) 2)} Lightwave
Philips TUV 4W = F4T5	T5		136	1	LPL-5-9	RMB-IP13-SI	LW20EB20-120-xx
Philips TUV 6W = F6T5	T5		212	1	LC-4-9-C	RMB-IP13-SI	LW20EB20-120-xx
Philips TUV 8W = F8T5	T5	1ft	288	1	LPL-5-9		LW20EB20-120-xx
				1	LPL-7-9		
				1	LC-4-9-C		
				2			
Philips TUV 11W = F11T5	T5		212	1	LC-14-20-C		LW20EB20-120-xx
Philips TUV 16W = F16T5	T5	1ft	288	1	LC-14-20-C	RMB-2P13-L2	LW20EB20-120-xx
Philips TUV 25W = F25T5	T5		517	1			LW20EB20-120-xx
Philips TUV 10W = F10T8	T8		332	1			
Philips TUV 15W = F15T8	T8	18"	437	1	LO-13-22	REL2P32-SC	LW20EB20-120-xx
				1	LC-14-20-C		
				1	L-120F		
Philips TUV 25W	T8	18"	437	1			LW20EB40-120-xx
Philips TUV F17T8	T8	2ft	590	1	RCN-IP32	REL IP32-SC	LW20EB20-120-xx
Philips TUV 30W = F30T8	T8	3ft	895	1			LW20EB40-120-xx
Philips TUV 36W	T8	4ft	1199	1		REL 1S40-SC	
				2		REL 2S40-SC	
Philips TUV 55W HO	T8	3ft	895	1		IUV-2S60-M4LD (120-277 main)	LW20EB65-PFC-xx
Philips TUV 75W HO	T8	4ft	1199	1		IUV-2S60-M4LD (120-277 main)	LW20EB65-PFC-xx
Philips TUV 115W VHO	T12	4ft	1199	1	RC2SI02-TP		
Philips TUV 36T5 SP	T5	3ft	842	1			LW20EB40-120-IN-xx
Philips TUV 36T5 4P-SE	T5	3ft	842	1		ICN2S39	LW20EB40-120-xx
Philips TUV 36T5 HO 4P-SE	T5	3ft	842	1		IUV-2S60-M4LD (120-277 main)	LW20EB65-PFC-xx
Philips TUV 64T5 SP	T5	5ft	1554	1		SSB21202/64-UV	LW20EB65-PFC-IN-xx
				2		SSB21202/64-UV	
Philips TUV 64T5 4P-SE	T5	5ft	1554	1		ICN1S80	LW20EB65-PFC-xx
Philips TUV 64T5 HO 4P-SE	T5	5ft	1554				IUV-2S60-M4LD (120-277 main)
Philips TUV PL-S 9W 2P			145	1	LPL-5-9-TP		LW20EB26-120
				1	LC-4-9-C-TP		
Philips TUV PL-S 9W 4P			145	1		RMB-IP13-L2	
				1		RMB-IP13-SI	
Philips TUV PL-S 11W 2P			214	1	N.A.		
Philips TUV PL-S 13W 2P			155	1	LC-13-TP		
				1	LO-13-22-TP		
Philips TUV PL-L 18W 4P			218	1	LC-25-TP	RMB-2P13-L2	LW20EB20-120-xx
Philips TUV PL-L 24W 4P			315	1		R-1BP27-TP	ICN2S24
Philips TUV PL-L 35W HO 4P			218	1		IUV-2S60-M4LD (120-277 main)	LW20EB40-120-xx
				2		IUV-2S60-M4LD (120-277 main)	
Philips TUV PL-L 36W 4P			408	1	R-1BP39-TP	REL-1TTS39	LW20EB40-120-xx
				1		ICN2S24	
				2	R-2BS39-TP	REL-2TTS39	
				2		ICN2S54	
Philips TUV PL-L 55W HF 4P			528	1		ICN1S80	LW20EB40-120-xx
Philips TUV PL-L 60W HO 4P			408	1		REL2SI10	LW20EB65-PFC-xx
				1		IUV-2S60-M4LD (120-277 main)	
				2		IUV-2S60-M4LD (120-277 main)	
Philips TUV PL-L 95W HO 4P			528	1		IUV-2S60-M4LD (120-277 main)	LW20EB65-PFC-xx

Philips TUV amalgam electronic drivers

Philips Lighting amalgam systems are being developed with the main municipal purification requirements in mind: high reliability, optimized lamp-ballast solution and high efficiency.

The printed circuit board with electronic components replaces the traditional copper/iron ballasts. By using electronic rather than magnetic ballasts, power losses are considerably reduced. By using our long history of electronic ballast development we are able to design the most reliable ballasts in the market. By potting our ballasts, our electronics will also survive in condensing and aggressive environments.

Features	Benefits
Optimized for driving Philips amalgam lamps	Optimal application performance
Fully automated production	High reliability and long lifetime



Philips TUV amalgam drivers									
Type T10	A (mm)	B (mm)	C (mm)	Line Frequency (Hz)	Main input (V)	Number of lamps	Lamp Power (W)	Lamp efficiency	Annual Failure Rate
Philips TUV 130W amalgam driver	283	297	694	50/60	110 - 240	1	146	>92%	<1%
Philips TUV 240W amalgam driver				50/60	110 - 240	1/2	243	>92%	<1%
Philips TUV 325W amalgam driver				50/60	110 - 240	1/2	270	>92%	<1%

Note: Philips TUV 240 and Philips TUV 325 are currently under development. Please contact us for more information. For lamp operating parameters please see Philips TUV extreme power technology amalgam lamps.

Philips quartz sleeves

Philips quartz realizes that UVC output is the most important product parameter for your UV and germicidal applications. Therefore we give continuous attention to control and improve the transmittance of our Ph 300 clear fused quartz.

We offer a broad range of sleeves, which are designed for Philips UV lamps. It is this perfect fit of lamp and sleeve which guarantees an excellent performance in your systems. Our sleeves are flame polished and can be closed at one end. The flame polished ends prevent breakage during handing. The resistance to pressure is max. 2700 PSI. Our sleeves are recognized for their constant and world-class quality and therefore applied by OEM industry leaders.

Especially for drinking water applications we developed Ph 300 Quartz sleeves. Ph 300 is the world-class quality standard on UVC transmittance at 253,7 nm.

Features	Benefits
Ideal fit with Philips UV lamps	High quality performance and long lifetime
Flame polished	No breakage during system assembly operations

Transmittance data Ph 300 clear fused quartz, n = > 100 samples.

Parameter	Typical value @ 253,7nm *	Specification @ 253,7nm	Unit
Absorption coefficient - Ph 300	0.142	0.332	cm ⁻¹
Transmittance Ph 300	90.7	89.0	%

* Transmittance measured at 1 mm wall thickness including surface reflection losses.

UV Transmittance Ph 300 clear fused quartz





Figure 1: Transmittance curve Ph 300 clear fused quartz, n = > 100 samples.



Product range dimensions

Philips Sleeves for T5 lamps					
Type T10	Outer diameter (mm)*	Outer diameter open end (mm) A *	Wall thickness (mm) B	Straight length (mm) C	Length incl. closed end (mm) D
Philips TUV 4P-SE 11W	25 ± 0,38	25 ± 0,58	1,2 ± 0,10	225 ± 2,0	240 ± 2,0
Philips TUV 4P-SE 16W	25 ± 0,38	25 ± 0,58	1,2 ± 0,10	300 ± 2,0	315 ± 2,0
Philips TUV 4P-SE 25W	25 ± 0,38	25 ± 0,58	1,2 ± 0,10	530 ± 2,0	545 ± 2,0
Philips TUV T5 4P-SE 36 HE&HO	25 ± 0,38	25 ± 0,58	1,2 ± 0,10	885 ± 2,0	900 ± 2,0
Philips TUV T5 4P-SE 64 HE&HO	25 ± 0,38	25 ± 0,58	1,2 ± 0,10	1585 ± 2,0	1600 ± 2,0
Sleeves for amalgam lamps					
Philips T 6 TUV XPT 130W	28 ± 0,42	28 ± 0,62	1,5 ± 0,12	885 ± 2,0	900 ± 2,0
Philips T 6 TUV XPT 325W	28 ± 0,42	28 ± 0,62	1,5 ± 0,12	1625 ± 2,0	1640 ± 2,0
Philips T 10 TUV XPT 330W	44 ± 1,32	44 ± 1,52	1,6 ± 0,16	1625 ± 2,0	1640 ± 2,0
Sleeves for PLS lamps (=SE)					
Philips TUV G23 PL-S 5W, 7W/9W	31 ± 0,62	31 ± 0,82	1,2 ± 0,12	129 ± 2,0	145 ± 2,0
Philips TUV G23 PL-S 11W/13 W	31 ± 0,62	31 ± 0,82	1,2 ± 0,12	129 ± 2,0	214 ± 2,0
Sleeves for PLL lamps (=SE)					
Philips TUV 2G11 PL-L 18W/35W HO	44 ± 1,32	44 ± 1,52	1,6 ± 0,16	195 ± 2,0	217 ± 2,0
Philips TUV 2G11 PL-L 36W/60W HO	44 ± 1,32	44 ± 1,52	1,6 ± 0,16	385 ± 2,0	407 ± 2,0
Philips TUV 2G11 PL-L 55W HF/95W HO	44 ± 1,32	44 ± 1,52	1,6 ± 0,16	505 ± 2,0	527 ± 2,0

Table 1: Product range Ph 300 clear fused quartz, sleeves.

* incl. tolerances of fire polishing

Notes: